

# SL700 5-Step Slit Lamp

The SL-700 5-step features improved resolution of 180k lux, reliably giving you a clean and clear image.

The illuminance of over 180k lux, allows the SL700 to meet the demands of fundus diagnosis, especially when the vitrella or vitreous opacities are distinctive.

The operating feel of the drum has been improved, as has the refractive degree range of the eyepiece, from +6.00D to -8.00D.

To make things more convenient for the user, when tuning the refractive degree of the eyepiece, the eyepiece cover does not turn along with it.

The compatibility to different brands of beam splitter and laser adaptor has also been improved.

01923 233980

[sales@graftonoptical.com](mailto:sales@graftonoptical.com)

 **[graftonoptical.com](http://graftonoptical.com)**

